



Pushing Performance
Since 1945



PEOPLE. POWER. PARTNERSHIP.

HARTING Han[®] S

Safe and error-free connections
in energy storage systems

HARTING Han® S

Solution overview and compliance to standards







HARTING Han® S

Key features and advantages







In line with the market trends for energy storage systems, Han® S was developed as a front mounting solution for high power transmissions with flexibility and safety. This single pole connector family can work with rated currents up to 200 A at a voltage of 1500 V, while assuring safe installations with finger safe contacts with different termination types (bolt or busbar) and visible control of the locking status. Moreover, the product is vibration proof and available in different colours, complete with a mechanical coding system that makes misconnections impossible.

Besides the fact of holding the brand-new approval UL 4128, Han® S provides important additional features currently not existing in the segment. As a matter of a fact, Han® S assures safe and error-free connections with high flexibility.

Han® S complies with all relevant standards for energy storage systems

-  **IEC 60664-1 (VDE 0110-0)**
Principles, requirements and tests
-  **IEC 61984 (VDE 0627)**
Connectors, safety requirements and tests
-  **UL 1977 (in release processing)**
Standard for component connectors for use in data, signal, control and power applications
-  **UL 4128**
Outline of investigation for intercell and intertier connectors for use in electrochemical battery system applications
-  **UL 1973**
Standard for batteries in use in stationary, vehicle auxiliary power and light electrical rail
-  **UL 9540**
Standard for energy storage and equipment



-  High power transmission in a compact design: rated currents up to 200 A at a voltage of 1500 V due to an effective contact resistance of less than 0.3 mΩ
-  Safe installations due to visible control of the locking status, finger protected contacts, mechanical & colour coding system and shock & vibration resistance
-  Easy (dis) assembly due to (un) screwing the contact of the screw mounted housing from the front. Easy mating through a self-opening single lever
-  High flexibility due to different mounting possibilities and contact terminations as well as 360° positioning for cable entry
-  Complies with all relevant energy storage standards, including the brand-new UL 4128
-  Free of lead and halogens

For more information refer to our homepage: www.HARTING.com/hans

HARTING Han[®] S

Technical characteristics

Inserts/electrical data acc. to DIN EN 60664-1 and DIN EN 61984

Number of contacts	1
Rated current	
- Han [®] S 120	120 A
- Han [®] S 200	200 A
Rated voltage	1500 V
Rated impulse voltage	8 kV
Pollution degree	2
Insulation resistance	≥ 10 ⁸ Ω
Contact resistance	≤ 0.3 mΩ
Limiting temperatures	-40 °C ... +125 °C
Number of mating cycles	≥ 500
Degree of protection acc. to IEC/EN 60529	Touch safe male and female contacts
- mated condition	IP40
- unmated condition	IP20 (1500 VDC, 1000 VAC)
Coding system	Mechanical & colour
Locking system	Single lever (with visible status)
Vibration and shock resistance acc. to IEC 16373	Category 1, class B
Cable entry	Angled, available rotation through 360°

HARTING Han[®] S

Technical characteristics

















Inserts/electrical data acc. to DIN EN 60664-1 and DIN EN 61984

Cable outer diameter	
- Han [®] S 120	5.5 -12.5 mm
- Han [®] S 200	6.4 -14.6 mm
Cable gland tightening torque	
- Han [®] S 120	1.5 Nm
- Han [®] S 200	2.5 Nm
Contact termination (hood)	Crimp (conductor cross-section 10 ... 50 mm ²)
- cable stripping length	22 mm
- suitable tools/crimp-dies	refer to the Han [®] S Assembly Instructions
Contact termination (housing)	Bolt/busbar
- recommended tightening torque	
• Han [®] S 120	4 Nm*
• Han [®] S 200	11 Nm*
Fixing screws (housing)	M3, 6 mm long, flat headed (acc. to ISO 7380-2)
- recommended tightening torque	0.5 - 0.8 Nm
Colour (hood/housing)	
- black	RAL 9005 (jet black)
- red	RAL 3001 (signal red)
- blue	RAL 5015 (sky blue)
Material (hood/housing)	Polyamide (PA)
Material (contacts)	Copper alloy
Material flammability class acc. to UL 94	V-0

* for bulkhead mounted housings, the use of a counter wrench is mandatory if applying more than recommended tightening torque.





HARTING Han® S

Components and part numbers

Han® S 120			
Identification/part no.	Figure	Drawings	
Rubber sleeve Cable outer diameter 5.5 – 7.0 mm 09 93 000 8220			
			
			
			
120 A female crimp contact, silver plated			
10 mm² conductor cross-section 09 93 000 8260			
16 mm² conductor cross-section 09 93 000 8261			
25 mm² conductor cross-section 09 93 000 8262			

HARTING Han® S

Components and part numbers

Han® S 120			
Identification/part no.	Figure	Drawings	
Angled hood, 10 ... 25 mm² conductor cross-section contact, incl. cable gland			
			Black 09 93 001 1501
Red 09 93 001 1502			
Screw mounted housing, incl. male contact with M6 bolt termination			
			Black 09 93 001 1101
Red 09 93 001 1102			

HARTING Han® S

Components and part numbers

Han® S 120		
Identification/part no.	Figure	Drawings
Bulkhead mounted housing, incl. male contact with M6 bolt termination Black 09 93 001 1301 Red 09 93 001 1302		
Bulkhead mounted housing, incl. male contact with busbar termination Black 09 93 001 1303 Red 09 93 001 1304		

Han® S 120 parts also available in blue colour, having an exclusive mechanical coding
 Han® S 120 housings also available with Unlocking Protected lever (unlocking only possible using a tool)
 Han® S 120 accessories available, such as protect cover for transport purposes and assembly tools





HARTING Han® S

Components and part numbers

Han® S 200		
Identification/part no.	Figure	Drawings
Cable outer diameter 6.4 – 7.9 mm 09 93 000 7221		
Cable outer diameter 7.7 – 9.2 mm 09 93 000 7222		
Cable outer diameter 9.0 – 10.5 mm 09 93 000 7223		
Cable outer diameter 10.3 – 11.8 mm 09 93 000 7224		
Cable outer diameter 11.6 – 13.1 mm 09 93 000 7225		
Cable outer diameter 12.9 – 14.6 mm 09 93 000 7226		
200 A female crimp contact, silver plated 25 mm ² conductor cross-section 09 93 000 7262 35 mm ² conductor cross-section 09 93 000 7263 50 mm ² conductor cross-section 09 93 000 7264		

HARTING Han® S

Components and part numbers





Han® S 200		
Identification/part no.	Figure	Drawings
Angled hood, 25 ... 50 mm ² conductor cross-section, contact incl. cable gland		
Hood Black 09 93 001 0501 Red 09 93 001 0502		
Screw mounted housing, incl. male contact with M8 bolt termination		
SMH/Bolt Black 09 93 001 0101 Red 09 93 001 0102		

For more information:
<https://b2b.harting.com/ebusiness/55956>



HARTING Han® S

Components and part numbers

Han® S 200		
Identification/part no.	Figure	Drawings
Bulkhead mounted housing, incl. male contact with M8 bolt termination		
BMH/Bolt Black 09 93 001 0301 Red 09 93 001 0302		
Bulkhead mounted housing, incl. male contact with busbar termination		
BMH/Busbar Black 09 93 001 0303 Red 09 93 001 0304		

Han® S 200 parts also available in blue colour, having an exclusive mechanical coding
 Han® S 200 housings also available with Unlocking Protected lever (unlocking only possible using a tool)
 Han® S 200 accessories available, such as protect cover for transport purposes and assembly tools
 Han® S 200 cable assemblies available



Pushing Performance
Since 1945

HARTING.com –
the gateway to your
country website

HARTING Technology Group
info@HARTING.com
www.HARTING.com